

OPTONICA

Instructions




LED Ring Fill Light

Thank you for choosing our product. This is a new type of LED ring fill light with built-in multi-lighting modes, which can switch among bright white, cold white, warm light. It can be used for indoors. Uniform light large diffusion range not, easy to expose, compact and lightweight, easy to carry, suitable for live video, makeup and studio etc.

Attention: Please read and follow all warnings and parameter configurations, keep this manual for further reference.

Description of Control



Installation of Tripod

- ① Pull out the tripod
- ② Open the tripod
- ③ Adjust height and screw the knob clockwise to lock it
- ④ Align the male head on top of the tripod to the female head of the light, twisting the ring light clockwise and tighten it.
- ⑤ By adjusting the ring light knob, you can adjust the angle according to the scene requirements.
- ⑥ Finished

Technical Data

Voltage: DC5V/2A

Power: 10W

Color temperature: 3000-6500k

Color rendering index: ≥ 80

Notes

1. Read the Manual carefully before usage.
2. Non professional users are forbidden to disassemble the light fitting with high voltage driver inside, or maintenance service won't be provided. All losses caused by the disassembly won't be taken by our company.
3. Keep switch off and detach the power supply cord to prevent from any losses caused by power link when the light fitting doesn't work.
4. Please pay attention to safety and prohibit falling, so as not to cause fire.

IMPORTER: Prima Group 2004 LTD, Bulgaria, 1784 Sofia, Mladost 1, bl. 144, Ground Floor; Phone: +359 2 988 45 72;